



# Variateurs à coupure de phase Dynalite

## DDLE801

8 channel Leading Edge Dimmer Controller at 1 A per channel

The Philips Dynalite DDLE801 supports eight channels of leading edge dimming at 1 A per channel. - It is suitable for use with incandescent lighting, as well as leading edge compatible magnetic and electronic transformers. - Advanced LED dimming technology makes the unit particularly suited to residential, retail and hospitality applications. - Active Load technology on each channelSoft start and voltage regulation technologiesSuperior internal drive componentry tuningFlexible mounting solution

### Données du produit

#### Caractéristiques générales

Marquage CE	Marquage CE
Remarques	Please download the Lighting - Product Data Sheet for more information and ordering options
Conforme à la directive RoHS UE	Oui

#### Conditions d'utilisation

Plage de températures ambiantes -5 à +40 °C


#### Données logistiques

Code de produit complet 871869600136300

Nom du produit de la commande	DDLE801
Code barre produit	8718696001363
Code de commande	00136300
Numérateur - Quantité par kit	1
Conditionnement par carton	1
SAP - Matériaux	913703061509
Poids net (pièce)	633.000 g

## Variateurs à coupure de phase Dynalite

### Schéma dimensionnel



Dynalite Leading Edge Dimmers

